

Recommended Xerox Media for Xerox® DocuColor® 5000

Version 4.0. August 2012

This supersedes any previous Recommended Media for Xerox DocuColor 5000

Important Notes:

Media recommendations made in this publication are based on qualification tests conducted using standard test images with moderate to heavy image area coverage. Test machines are maintained within specifications defined by user documentation.

* Testing environment: Temperature 23°C±2, Relative Humidity range 20-50%.

Reliability is based on your operating environment and application mix.

Machine reliability specifications may be affected by high usage of heavy weight and specialty stocks. In addition, variances in machine reliability may occur due to extended use of some media types.

Warranty disclaimer:

Xerox makes no guarantees or warranties, either expressed or implied, concerning the performance, use or replacement of non-Xerox branded media or throughput products. Customers should inquire directly of their paper distributor or manufacturer for any guidance when purchasing a particular media product for the first time, customers are advised to purchase small quantities to ensure that their expectations are met. The quality of Xerox supplies is consistent from ream to ream and is backed by a 100 % guarantee. The quality of non-Xerox branded paper may vary from ream to ream or carton to carton, so for optimum performance on Xerox Colour equipment, use only the best - Xerox supplies.

©2006-2012 Xerox Corporation. All rights reserved.

XEROX®, XEROX and Design® and DocuColor® are trademarks of or licensed to Xerox Corporation in the United States and/or other countries.

For the latest line of Xerox supplies contact your local Xerox representative or a recommended distributor. For the most recent version of this list visit www.xerox.com/europaper

European Recommended Materio	IIS LIST - DO	CuColol 3	0000		Grane														
		Standard Cut Sizes			Grammage Weight (g/m2)			DC5000 Trays/Weight Selection and Best Practices for Operation											
		A4 A3 SRA3 210x297 mm 297x420 mm 320x450 mm		Weight of the paper in grams per square meter	IOT: Trays 1 and 2 SFM: Trays 3 and 4		IOT: Trays 1 and 2 SFM: Trays 3 and 4		IOT: Trays 1 and 2 SFM: Trays 3 and 4		IOT: Trays 1 and 2 SFM: Trays 3 and 4		IOT: Trays 1 and 2 SFM: Trays 3 and 4		IOT: Trays 1 and 2 SFM: Trays 3 and 4				
Weight Range Specification			>				0 gsm		05 gsm	106-1	135 gsm	136-18			20 gsm	221- 300 gsm			
Instructions for Printing one side (Simplex) or two sides (Duplex) Business Papers (Bond, xerographic,	Decurler Setting		->		1	Simplex	Duplex	Simplex	Duplex	Simplex	Duplex	Simplex	Duplex	Simplex	Duplex	Simplex	Duplex		
and laser grades)	paper type																		
Xerox Colour Impressions 80 gsm	А		003R97662		80	OK All Trays	OK All Trays												
		003R97661		003R98840	80 90	OK All Trays	OK All Trays	OK All Trays	OK All Trays			1				 			
Xerox Colotech+ Gold 90 gsm	Α		003R98839	0031(30040	90			OK All Trays	OK All Trays							<u> </u>			
•		003R98837		003005030	90			OK All Trays	OK All Trays							_			
Xerox Colotech+ 90 gsm	А		003R94642	003R95838	90 90			OK All Trays OK All Trays	OK All Trays OK All Trays							 			
		003R94641			90			OK All Trays	OK All Trays										
V C-laur I	A		003R97664	003R97665	90 90			OK All Trays	OK All Trays										
Xerox Colour Impressions 90 gsm	^	003R97663	003897664		90			OK All Trays OK All Trays	OK All Trays OK All Trays										
				003R98845	100			OK All Trays	OK All Trays										
Xerox Colotech+ Gold 100 gsm	Α	003R98842	003R98844		100			OK All Trays OK All Trays	OK All Trays OK All Trays							 	 		
		303R30042		003R95839	100	1		OK All Trays	OK All Trays		+	†		1		 	 		
Xerox Colotech+ 100 gsm	Α		003R94647		100			OK All Trays	OK All Trays										
		003R94646	003R97103		100			OK All Trays OK All Trays	OK All Trays										
Xerox Colotech Natural White 100 gsm	A	003R97102	003897103		100			OK All Trays	OK All Trays							-			
Xerox Colour Impressions 100 gsm				003R97668	100			OK All Trays	OK All Trays										
	Α	003R97666	003R97667		100			OK All Trays OK All Trays	OK All Trays OK All Trays							ļ			
		003897666		003R98849	120			OK All Trays	OK All Trays	OK All Trays	OK All Trays								
Xerox Colotech+ Gold 120 gsm	В		003R98848		120					OK All Trays	OK All Trays								
		003R98847		003R95840	120 120					OK All Trays	OK All Trays					.			
Xerox Colotech+ 120 gsm	В		003R94652	003893640	120					OK All Trays OK All Trays	OK All Trays OK All Trays					-			
		003R94651			120					OK All Trays	OK All Trays								
Xerox Colour Impressions 120 gsm	A		003R97669	003R97670	120					OK All Trays	OK All Trays					ļ			
Aerox Colodi Impressions 120 gsm	^	003R98685	003897669		120 120					OK All Trays OK All Trays	OK All Trays OK All Trays					-			
Uncoated Heavy Stocks	Decurler Setting								1	,									
	paper type			003R98686	160				1		1	OK All Trays	OK All Trays						
Xerox Colour Impressions 160 gsm	A		003R98008	003K98080	160							OK All Trays	OK All Trays						
		003R98007			160							OK All Trays	OK All Trays						
Xerox Colotech+ Gold 160 gsm	A		003R98854	003R98855	160 160							OK All Trays OK All Trays	OK All Trays OK All Trays			-			
Aciox colotechi dola 100 gsili	^	003R98852	00383634		160							OK All Trays	OK All Trays						
				003R95841	160							OK All Trays	OK All Trays						
Xerox Colotech+ 160 gsm	Α	003R94656	003R94657		160 160							OK All Trays OK All Trays	OK All Trays OK All Trays			<u> </u>	-		
Variation Callata at Material William 160 anns		003134030	003R95957		160							OK All Trays	OK All Trays						
Xerox Colotech Natural White 160 gsm		003R95956			160							OK All Trays	OK All Trays						
Xerox Colotech+ Gold 200 gsm	A		003R97968	003R97969	200									OK All Trays OK All Trays	OK All Trays OK All Trays				
Aerox Colotecti+ dola 200 gsiii	^	003R97967	003897966		200									OK All Trays	OK All Trays	-			
				003R95842	200									OK All Trays	OK All Trays				
Xerox Colotech+ 200 gsm	A	003R94661	003R94662		200									OK All Trays OK All Trays	OK All Trays OK All Trays	 	 		
Variation Callatanta Material Military 200 anns		100000001	003R95959		200									OK All Trays	OK All Trays				
Xerox Colotech Natural White 200 gsm	Α	003R95958			200									OK All Trays	OK All Trays				
Yerey Calatach Gold 220 gcm			003R97972	003R97973	220	-					1	-		OK All Trays	OK All Trays	 	 		
Xerox Colotech+ Gold 220 gsm	A	003R97971	003K9/9/2		220 220				+		+	1		OK All Trays OK All Trays	OK All Trays OK All Trays	 	 		
				003R95843	220									OK All Trays	OK All Trays				
Xerox Colotech+ 220 gsm	A	003004660	003R94669		220	ļ					1	1		OK All Trays	OK All Trays	 			
		003R94668			220	l	1		1	1	1	l .	1	OK All Trays	OK All Trays				

Page 2 of 5 Revision 4.0 August 2012

European Recommended Mater	iuis List - D0	cucoioi .	0000		Grammaa													
			Standard Cu	t Sizes	Grammage Weight (g/m2)	DC5000 Trays/Weight Selection and Best Practices for Operation												
		A4 210x297 mm	A3 297x420 mm	SRA3 320x450 mm	Weight of the paper in grams per square meter	IOT: Trays 1 a SFM: Trays 3 a	ınd 4	SFM: Tra	ys 1 and 2 ys 3 and 4	SFM: Tro	ays 1 and 2 ays 3 and 4	SFM: Tray		SFM: Tra	ys 1 and 2 ys 3 and 4	SFM: Tra	iys 1 and 2 iys 3 and 4	
Weight Range Specification			>			60-80 gsm			05 gsm		135 gsm		6 gsm		20 gsm		300 gsm	
Instructions for Printing one side (Simplex) or two sides (Duplex) Uncoated Heavy Stocks	Decurler Setting	I	>		T .	Simplex [Duplex	Simplex	Duplex	Simplex	Duplex	Simplex	Duplex	Simplex	Duplex	Simplex	Duplex	
Oncoured Heavy Stocks	paper type																	
				003R98977	250											OK All Trays	Manual Duplex	
Xerox Colotech+ Gold 250 gsm	Α	003R98975	003R98976		250 250											OK All Trays	Manual Duplex Manual Duplex	
		003896973		003R95844	250						1					OK All Trays	Manual Duplex Manual Duplex	
Xerox Colotech+ 250 gsm	A		003R94672		250											OK All Trays	Manual Duplex	
		003R94671			250											OK All Trays	Manual Duplex	
Xerox Colour Impressions 250 gsm	A		003R97671	003R97672	250 250											OK All Trays	Manual Duplex	
Aerox Colour Impressions 230 gsin	_ ^	003R98687	003897671		250											OK All Trays	Manual Duplex Manual Duplex	
		003K98087		003R97981	280											OK All Trays	Manual Duplex	
Xerox Colotech+ Gold 280 gsm	A		003R98980		280											OK All Trays	Manual Duplex	
		003R98979		002007000	280											OK All Trays	Manual Duplex	
Xerox Colotech+ 280 gsm	Α		003R97098	003R97099	280 280											OK All Trays OK All Trays	Manual Duplex Manual Duplex	
Acrox Colotectii 200 gain		003R97097	0031(37030		280											OK All Trays	Manual Duplex	
				003R97985	300											OK All Trays	Manual Duplex	
Xerox Colotech+ Gold 300 gsm	A		003R97984		300											OK All Trays	Manual Duplex	
		003R97983			300											OK All Trays	Manual Duplex	
Xerox Colotech+ 300 gsm	A		003R97553	003R97554	300 300											OK All Trays	Manual Duplex	
	_ ^	003R97552	003K9/553		300											OK All Trays OK All Trays	Manual Duplex Manual Duplex	
Coated Text or Book Stocks	Decurler Setting	0031(37332			300				1		II.				l .	OK All Huys	Mulidui Duplex	
C2S	paper type																	
223	puper type			003R90357	120					OK All Trays	OK All Trays							
Xerox Colotech+ Silk Coated 120 gsm	A		003R90356		120					OK All Trays	OK All Trays							
		003R90355		002000220	120					OK All Trays	OK All Trays							
Xerox Colotech+ Gloss Coated 120 gsm	A		003R90337	003R90338	120 120					OK All Trays OK All Trays	OK All Trays OK All Trays							
Acrox colotectiv closs couted 120 gsin	_ ^	003R90336	0031(3033)		120					OK All Trays	OK All Trays						+	
				003R90360	140							OK All Trays	OK All Trays					
Xerox Colotech+ Silk Coated 140 gsm	A	003R90358	003R90359		140 140							OK All Trays	OK All Trays					
		003890358		003R90341	140	+						OK All Trays OK All Trays	OK All Trays OK All Trays					
Xerox Colotech+ Gloss Coated 140 gsm	A		003R90340	0031(30341	140							OK All Trays	OK All Trays					
		003R90339			140							OK All Trays	OK All Trays					
Coated Heavy Stocks	Decurler Setting																	
C2S	paper type																	
v				003R90363	170							OK All Trays	OK All Trays					
Xerox Colotech+ Silk Coated 170 gsm	A	003R90361	003R90362		170 170							OK All Trays OK All Trays	OK All Trays OK All Trays					
		0031(30301		003R90344	170							OK All Trays	OK All Trays				+	
Xerox Colotech+ Gloss Coated 170 gsm	A		003R90343		170							OK All Trays	OK All Trays					
		003R90342			170							OK All Trays	OK All Trays					
Xerox Colotech+ Silk Coated 210 gsm	A		003R90365	003R90366	210 210									OK All Trays	OK All Trays		-	
Aerox Colotecti+ Silk Couteu 2 10 gsili	_ ^	003R90364	003890365		210									OK All Trays OK All Trays	OK All Trays OK All Trays		+	
				003R90347	210									OK All Trays	OK All Trays		+	
Xerox Colotech+ Gloss Coated 210 gsm	A		003R90346		210									OK All Trays	OK All Trays			
		003R90345		003R90369	210 250									OK All Trays	OK All Trays			
Xerox Colotech+ Silk Coated 250 gsm	A		003R90368	003890369	250											OK All Trays OK All Trays	Manual Duplex Manual Duplex	
Action Colorectiff Still Couled 250 golff		003R90367	111.00000		250						<u> </u>	<u> </u>				OK All Trays	Manual Duplex	
			0005	003R90350	250											OK All Trays	Manual Duplex	
Xerox Colotech+ Gloss Coαted 250 gsm	A	003R90348	003R90349		250 250					1	1	1				OK All Trays	Manual Duplex	
		UU3K9U348		003R90372	250	 		1		1	1	+		1		OK All Trays OK All Trays	Manual Duplex Manual Duplex	
Xerox Colotech+ Silk Coated 280 gsm	A		003R90371	003.00072	280	1				1		1		t		OK All Trays	Manual Duplex	
		003R90370			280											OK All Trays	Manual Duplex	
Year Calabada Class Control 200			00000000	003R90353	280											OK All Trays	Manual Duplex	
Xerox Colotech+ Gloss Coated 280 gsm	A	003R90351	003R90352		280 280			-	-	+		1		-		OK All Trays	Manual Duplex Manual Duplex	
	l	ICCORNCOO			200	1 1		1		1		1	1		1	UK All Trays	munual Duplex	

Page 3 of 5 Revision 4.0 August 2012

European Recommended Materia	IIS LIST - DO	CuColoi .	1000														
					Grammage												
		Standard Cut Sizes			Weight (g/m2)				DC50	000 Trays/W	eight Selectio	n and Best Pro	actices for Ope	ration			
				SRA3 320x450 mm	Weight of the paper in grams per square meter	IOT: Trays 1 and 2 SFM: Trays 3 and 4		IOT: Trays 1 and 2 SFM: Trays 3 and 4		IOT: Trays 1 and 2 SFM: Trays 3 and 4		IOT: Trays 1 and 2 SFM: Trays 3 and 4		IOT: Trays 1 and 2 SFM: Trays 3 and 4			ays 1 and 2 ays 3 and 4
Weight Range Specification			>			60-8		81-105 gsm		106-135 gsm		136-186 gsm		187-220 gsm			300 gsm
Instructions for Printing one side (Simplex) or two sides (Duplex)			· >			Simplex	Duplex	Simplex	Duplex	Simplex	Duplex	Simplex	Duplex	Simplex	Duplex	Simplex	Duplex
Super Gloss Coated Heavy Stocks C1S	Decurler Setting paper type																
Xerox Colotech+ Supergloss 135 gsm Image quality will not be as good on second side	Α	Select 106-135 gsm n 003R97679	ode. Load with coated	d side up.	135							OK All Trays	OK All Trays]
Thiage quality will not be as good on second side	-		ode. Load with coated	d side up	133					+		OK All Trays	OK All Trays				
Xerox Colotech+ Supergloss 160 gsm	A	Select 107-220 g31111	003R97681	a side up.	160									OK All Trays	OK All Trays		
Image quality will not be as good on second side	^	003R97680	0031(37001		160									OK All Trays	OK All Trays		
V 61: 1 6 1 849	-	0031(37 000		003R97684	210					+			_	OK All Trays	OK All Trays		
Xerox Colotech+ Supergloss 210 gsm	Α		003R97683	003K37084	210									OK All Trays	OK All Trays		+
Image quality will not be as good on second side	A	003R97682	0031(37003														+
					210									OK All Trays	OK All Trays		
Xerox Colotech+ Supergloss 250 gsm		Select 221-300 gsm n	ode. Load with coated	003R97688	250											OK All Trays	Manual Duplex
Image quality will not be as good on second side	A		003R97687	UU3K97688	250					1						OK All Trays OK All Trays	Manual Duplex Manual Duplex
		003R97686	003897087		250											OK All Trays	Manual Duplex
Specialties	Decurler Setting paper type		I	ll .	Various				·		II.		1				
Xerox Colotech Supergloss 210 A4 Prescored White	Α	Second side image qu 003R97685	ality will not be as goo	d as side one.	210									OK All Trays	OK All Trays		
Xerox ValuPerfCard Uncoated 500 sheet box	А	Maximum of 50 sheet 003R97690	stacks		216									OK All Trays	OK All Trays		
			220 gsm mode. Load i	mage side up.													
Xerox DuraPaper	Α			003R97513	250 microns											OK All Trays	Manual Duplex
Xerox Laser Business Cards 10-up	А	Select Uncoated 187- 003R97512	220 gsm mode - image	side up.	195									OK All Trays	Manual Duplex		
Xerox Colotech Supergloss Document Folder			gsm mode for glossy	side, Uncoated 221- 003R97634	250											OK All Trays	Manual Duplex
Tab Stock	Decurler Setting paper type			0031(97034	230				1						1		
Xerox Colotech Tabs White 100x5 Reverse Collated	В	Feed long edge first, t 003R97231	abs trailing.		200					1	1			OK All Trays	OK All Trays		
Xerox Colotech Tabs White 50x10 Reverse Collated	В	003R97231			200					1		1		OK All Trays	OK All Trays		
Xerox Reinforced Tabs White 100x5 Reverse Collated		003R97232 003R97229			200		-	1	-	-	-	1	+	· ·			
Xerox Reinforced Tabs White 100x10 Reverse Collated Xerox Reinforced Tabs White 100x10 Reverse Collated	B R	003R97229 003R97230			200		 	<u> </u>	1	+	+	 	+	OK All Trays	OK All Trays		
Aerox Reinforced Tabs White Tuux Tu Reverse Collated	В	UU3K9/230			200	l .		1		<u> </u>		l		OK All Trays	OK All Trays		

^{*} Feed Long Edge First, Tabs Trailing

Page 4 of 5 Revision 4.0 August 2012

European Recommended Materials	LIST - DO	cucolor:	5000															
			Standard Cu	t Sizes	Grammage Weight (g/m2)	DC5000 Trays/Weight Selection and Best Practices for Operation												
		A4 A3 SRA3		SRA3	Weight of the paper in grams per square	IOT: Trays 1 and 2 SFM: Trays 3 and 4		IOT: Trays 1 and 2 SFM: Trays 3 and 4		IOT: Trays 1 and 2 SFM: Trays 3 and 4	IOT: Trays 1 and 2 SFM: Trays 3 and 4		IOT: Trays 1 and 2 SFM: Trays 3 and 4		IOT: Trays 1 and 2 SFM: Trays 3 and 4			
Weight Range Specification		210x297 mm	297x420 mm	320x450 mm	meter	60-80 gsm		81-105 gsm		106-135 gsm	136-186 qsm		187-220 gsm			800 qsm		
Instructions for Printing one side (Simplex) or two sides (Duplex)			>			Simplex	Duplex	Simplex	Duplex	Simplex Duplex	Simplex	Duplex	Simplex	Duplex	Simplex	Duplex		
Transparencies	Decurler Setting	1																
	paper type																	
V	Default	Select Uncoated 221-30	0 gsm mode. Load transpa	rency facing up.														
Xerox Universal Transparency with Paper Backing	Derduit			003R98201	100 micron										OK All Trays	4		
		003R98199			100 micron										OK All Trays	4		
V	Default	For high speed (standa Select Uncoated 187-22	0 gsm mode. Load transpa	rency facing up.														
Xerox Universal Transparency with Paper Backing	Derduit	002000400		003R98201	100 micron								OK All Trays					
	Decurler Setting	003R98199			100 micron Label Stock								OK All Trays					
Label Stock	paper type	1			(Approximately)													
Xerox Colour Laser Printer Labels		002002072			400								OK All Trays					
1 per A4 6 per A4	1 _	003R93872 003R93873			190 190		1						OK All Trays OK All Trays			+		
8 per A4	С	003R93874			190								OK All Trays			+		
14 per A4		003R93875			190								OK All Trays					
24 per A4		003R97524			190								OK All Trays					
Xerox Colotech+ Gloss Labels A4 1-up Xerox Colotech+ Matt 2-up CD Labels and CD Inserts Combi Box	C&A	003R97288 003R97515			190 190 & 120								OK All Trays OK All Trays		-			
Xerox Durapaper Label (polyolefin face material) 1 PER A4	C	003R97313			250								OK All Huys		OK All Trays			
Nerox burapaper Easter (poryoienin race material) 11 Ek 714			0 gsm mode. Load image s	ide up.	230										OKAM Hays	+		
Xerox Glossy White Self Adhesive Label for Conventional Toner	Default			003R97348	190								OK All Trays					
	B 1 6	003R97245			190								OK All Trays					
Carbonless Paper	Decurler Setting paper type	Fan must be disabled	I prior to use*															
Xerox Premium Digital Carbonless Paper					Approximately													
CB Singles White		003R99069			82			OK All Trays										
CB Singles White (Perforated along long edge)		003R99088 003R99080			82			OK All Trays OK All Trays							-	+		
CB Singles Yellow CB Singles Pink	=	003R99080 003R99083			82 82			OK All Trays							-			
CB Singles Pilik		003R99082			82			OK All Trays										
CB Singles Green		003R99081			82			OK All Trays										
CFB Singles White		003R99070			86			OK All Trays										
CFB Singles Yellow		003R99071			86			OK All Trays										
CFB Singles Yellow (Perforated along long edge) CFB Singles Pink	_	003R99091 003R99074			86 86			OK All Trays OK All Trays							—	+		
CFB Singles Pink (Perforated along long edge)		003R99093			86			OK All Trays							 	+		
CFB Singles Blue		003R99072			86			OK All Trays								 		
CFB Singles Green		003R99073			86			OK All Trays										
CF Singles White		003R99075			82			OK All Trays										
CF Singles Yellow		003R99076			82			OK All Trays										
CF Singles Pink CF Singles Blue	A	003R99077 003R99078			82 82			OK All Trays OK All Trays								+		
CF Singles Bide CF Singles Green		003R99079			82			OK All Trays								+		
A4+ CF Singles Yellow		003R99639			82			OK All Trays										
A4+ CF Singles Pink		003R99638			82			OK All Trays										
CF Singles Tag Cream		003R99146			170								OK All Trays					
CF Singles Tag White		003R99147			170								OK All Trays					
A4+ CF Singles Tag Cream A4+ CF Singles Tag Pink	-	003R99640 003R99641			170 170			-					OK All Trays OK All Trays			-		
2-Part White/Yellow		003R99105	003R99133		82/82			OK All Trays			†		Olivia ridys		 	+		
2-Part White (Perforated along long edge)/Yellow	1	003R99084			82/82		1	OK All Trays			1				t e	 		
2-Part White/Pink		003R99107	003R99134		82/82			OK All Trays										
3-Part Straight White/Yellow/Pink		003R99108	003R99135		82/86/82			OK All Trays										
3-Part Straight White (Perforated LE)/Yellow (Perforated LE)/Pink	_	003R99086			82/86/82			OK All Trays							1			
3-Part Reverse Pink/Yellow/White	4	003R99109			82/86/82			OK All Trays							├			
4-Part Straight White/Yellow/Pink/Blue 4-Part Reverse Blue/Pink/Yellow/White		003R99111 003R99112			82/86/86/82		1	OK All Trays OK All Trays			-		-			+		
4-ruit Reverse bille/Pink/Tellow/White	l	003K99112			82/86/86/82	l .	1	UK All Trays		1	1	1	1	1				

 $^{^\}star$ Contact your local Service Representative and refer to System Administration Guide for details

Page 5 of 5 Revision 4.0 August 2012