Xerox® 700i/770 European Custom Media List - May 2012

The Xerox CUSTOM Media List contains custom media that has been tested on the Xerox 700 i/770 for image quality and performance. Custom media on this list are digitally optimized, designed and manufactured for performance in Xerox digital printing equipment. Best Practices for Operation are outlined below. Customers should validate the Best Practices for Operation are acceptable for their application. <u>*Any alterations to the product's basic design, including sheet size, must be tested and approved by the Xerox Media & Compatibles Technology Center.</u> When purchasing a particular media product for the first time, customers are advised to purchase small quantities to insure that expectations are met. CUSTOM media may be ordered through a Xerox Supply Account Manager.

			Size Tested				Xerox 700i/770 Trays / Weight Selection and Best Practices for Operation				
								X700i/770 Weight			
		Decurler Setting	A4	A3	SRA3	Other		Selection (Media	Food Trav	Best Practices for Operation	
Photo Media		Setting	A4	AS	SKAS	Other	Grammage	Type)	Feed Tray	best Practices for Operation	
	rd Mode" only if using Xerox 770										
•	, , ,									Image quality degradation /deletions may occur if imaged over perforations, die cuts and scores. Maintain un-imaged clearances of 3mm.	
Xerox FunFlip		Default				003R96904 216 x 279 mm (8.5"x11")		151 - 176 gsm (Coated) Simplex Only	Tray 5 MSI / Bypass	Single sheet from Tray 5/MSI Bypass. Simplex only application.	
						++				Registration variability +/- 2.3 mm.	
Xerox AccordianPix						003R96905		221 - 256 gsm (Label) Simplex Only		Image quality degradation /deletions may occur if imaged over perforations, die cuts and scores. Maintain un-imaged clearances of 3mm.	
		Default				216 x 356 mm (8.5"x11")			Tray 5 MSI / Bypass	Single sheet in Short Edge Feed (SEF) orientation from Tray 5/MSI Bypass. Simplex only application.	
						(8.3 X11)				Registration variability +/- 2.3 mm.	
						003R96902		177 - 220 gsm (Coated) Simplex / Manual	Tray 5 MSI / Bypass	Bind must be run on trailing edge.	
Yorox EverElat		Auto	003R96901			330 x 320 mm	n			Do not image over the bind area.	
Xerox EverFlat		Auto	Landscape			003R96903 330 x 330 mm		Duplex Only	Tray 5 MS17 Bypass	Fan sheets thoroughly before loading into Tray 5 / MSI Bypass Tray	
										Deletions may occur in the bind area with high area coverage / full bleed applications	
Translucent Paper					1						
Compatible with "Standar	rd Mode" only if using Xerox 770	1									
Xerox Translucent 105 gsm		Default	007R96577				105	106-128 (Coated) Simplex Only	Any tray	Acclimatise paper at printer environment for at least 24 hours prior to running. Sheets should be fanned gently before loading into the feed tray. Feed from all trays. Fan sh well before loading. Simplex only application.	
Xerox Translucent 135 gsm		Default	007R99402				135	151-176 gsm (Coated) Simplex Only	Any tray	Acclimatise paper at printer environment for at least 24 hours prior to running. Sheets should be fanned gently before loading into the feed tray. Feed from all trays. Fan sh well before loading. Simplex only application.	
Digiboard											
Compatible with "Standard Xerox Digiboard	rd Mode" only if using Xerox 770		1			T		1			
	Variety Pack CD Wallet		-		003R96921				1		
			-		003R96907			177-220 gsm (Coated) Simplex Only and Face up	Tray 5, Trays 6 & 7 OHCF	Acclimatise paper at printer environment for at least 24 hours prior to running. Sheets should be fanned gently before loading into the feed tray. Feed from Tray SMS1, single sheet loading only. Trays 6 & 7 OHCF: fan sheets before loading. Simplex only. Face up printing. Avoid printing within 5 mm of perforations and creases.	
	A4 Folder				003R96908		210				
	Tent Card AS Folder				003R96909 003R96910						
	Pillow Pack	Set at A			003R96910 003R96911						
Trim & Tape	Mug Box	SecurA	-		003R96911	-					
	Wine Sleeve				003R96912						
	Business Card Box				003R96914						
	Tent Card Tall				003R96915						
	A4 Show Card				003R96916						
Xerox Digiboard Perforated & Tabbed	Variety Pack				003R96822		-	177-220 gsm (Coated) Simplex Only and Face up	Tray 5, Trays 6 & 7 OHCF	Acclimatise paper at printer environment for at least 24 hours prior to running. Sheets should be fanned gently before loading into the feed tray. F feed from Tray SMSI, single sheet loading only. Trays 6 & 7 OHCF: fan sheets before loading. Simplex only. Face up printing. Avoid printing within 5 mm of perforations and creases.	
	Tent Card				003R96919						
	Mug Box				003R96922						
	Wine Sleeve				003R96923						
	Tent Card Tall				003R96925						
		Set at A			003R96924	1	210				
	Door Hanger				003R96926	1	1				
	Golf Ball Box				003R96818	1	1				
	Desk Tidy				003R96819		-				
	Gift Box Lid				003R96820	1					
Xerox Digiboard	Gift Box Base					003R96821		Not applicable	Not applicable	Base box for 003R96820. Not for printing	

		Size Tested				Xerox 700i/770 Trays / Weight Selection and Best Practices for Operation				
	Decurler Setting	A4	A3	SRA3	Other	Grammage	X700i/770 Weight Selection (Media Type)	Feed Tray	Best Practices for Operation	
Premium NeverTear Polyester Compatible with "Standard Mode" only if using Xerox 770										
Xerox Premium NeverTear 95µm		003R98056		003R98031			129-150 (Coated) Simplex / Manual Duplex Only	Tray 5, Trays 6 & 7 OHCF	Select Face-Up Delivery to the Offset Catch Tray. Stacking may be compromised due to static. Not intended for extensive/exclusive usage.	
Xerox Premium NeverTear 120µm		003R98058		003R98035			151-176 (Coated) Simplex / Manual Duplex Only	Tray 5, Trays 6 & 7 OHCF	Select Face-Up Delivery to the Offset Catch Tray. Stacking may be compromised due to static. Not intended for extensive/exclusive usage.	
Xerox Premium NeverTear 145µm		003R98091		003R98039			177-220 (Coated) Simplex / Manual Duplex Only	Tray 5, Trays 6 & 7 OHCF	Select Face-Up Delivery to the Offset Catch Tray. Stacking may be compromised due to static. Not intended for extensive/exclusive usage. Image quality may be improved using a Custom Paper setting with Image Transfer set to 150%.	
Premium NeverTear Synthetic Labels Compatible with "Standard Mode" only if using Xerox 770										
Matt White Polyester, Permanent Adhesive		007R92024				221	221-256 gsm (Label) Simplex only	Tray 5 MSI / Bypass	Load tray with sheets short edge feeding first (SEF). Deliver sheets in face-up orientation.	
Gloss White Polyester, Permanent Adhesive		007R92031				236	177-200 gsm (Label) Simplex only	Tray 5 MSI / Bypass	Stacking may be compromised due to high static levels in the sheet	
Glass Clear Polyester, Permanent Adhesive		007R92038				217	177-200 gsm (Label) Simplex only	Tray 5 MSI / Bypass	Stacking may be compromised due to high static levels in the sheet	
Frosted Polyester, Permanent Adhesive		007R92045				195	177-200 gsm (Label) Simplex only	Tray 5 MSI / Bypass	Load tray long edge feeding first (LEF) and deliver in face-up orientation.	
Glass Clear Polyester, Low Tack Adhesive		007R92052				209	177-200 gsm (Label) Simplex only	Tray 5 MSI / Bypass	Stacking may be compromised due to high static levels in the sheet	